

>



Model Number: F36-220v

Clean Storm Forte F36-220v HEPA Concrete Grinder Dust Extractor Collector 3 Motor Vacuum 220 Volt 18 amp 354 CFM

Manufacturer: Clean Storm

Clean Storm Forte F36-220v HEPA Concrete Grinder Dust Extractor Collector 3 Motor Vacuum 220-240 Volt 13 amp Three-Motor and Two-Stage Filtering System, Single-phase HEPA Dust Extractor

Description

Clean Storm F-36 HEPA Dust Extractor with two stage Filtering System

Clean Storm F-36 HEPA Dust Extractor Vacuum features 3 individual Motors: each motor has its own individual switch to control on/off. This option allows professionals to choose how many motors to run, based on individual project scenarios, which will save energy and extend switch life and product lifespan.

Clean Storm F-36 Dust Extractor Machine with 2 phase filtering system, including a 1st stage pre conical filter as well as a second stage HEPA H13 Filter. The HEPA filter is individually tested and certified complying H13 EN1822:2209. Equipped with the HEPA H13 Filter, the Forte F-36 Vacuum can separate 0.3um dust with an efficiency >99.7%, ensuring a high standard of quality and safety.

Clean Storm F36 HEPA Extractor Vacuum has a strong, sturdy frame made of all metal, as well as 4 pieces of frame that add additional support to strengthen the frame structure. Much stronger frame than comparable brands that do not have the additional metal frame support. Ensures safety for operators of the machine, as well as preventing accidental damage from structural failure that might lead to damage. The Clean Storm F-36 hepa dust extractor machine uses a unique reverse-air cleaning technology, which safely and conveniently cleans the filter in an effective way. Reverse Air Cleaning system prevents dust and debris from clogging the filter, and thereby maintaining a consistent, normal airflow. With the technology, you do not have to open a vacuum to clean filter and create a potentially dangerous dust hazard.

Another unique feature from Clean Storm F36 Dust Extractor is the solid 10 inch non marking tires - round, solid rubber wheels. Non marking on all surfaces, including wood, carpet, and all flooring surfaces. Prevent damage from moving the equipment wherever needed, as well as piece of mind while climbing stairs and different levels. Forte easy release clip to make filter changing process much easier and faster than with comparable machines from other brands.

Forte Tools features a special designed switch replacement panel, shortening switch replacement time to just a few minutes. F36 has an easy cleaning system, including 4 piece ball plunger system ( vs. 2 piece for other machines) to smoothen out inlet plate sliding up/down process

Video at : [https://youtube.com/shorts/AbJ\\_VM9MdCY?feature=share](https://youtube.com/shorts/AbJ_VM9MdCY?feature=share)

Specifications

CS8265C Plug

13 amps @ 240 Volts

Triple 2 stage 1200 watt vacuum motors.

Dual Hepa Filters

>

Weight 54 KG  
20 ft 8-3 Power cord.  
354 Open flow / Filters removed CFM (Steambrite Tested 308.1 CFM)  
90" Water Lift (Steambrite tested 97.8")

Shipping  
35"Lx26"Wx59 " H ,  
275 IBS

Factory Installed Triple  
Ametek Lamb 119656-00, Vacuum motor, 240 volt 2 stage, Peripheral  
Discharge 5.7 Diameter

Normal  
0

false  
false  
false

EN-US  
X-NONE  
X-NONE

>

DefSemiHidden="false" DefQFormat="false" DefPriority="99"  
LatentStyleCount="376">

UnhideWhenUsed="true" QFormat="true" Name="heading 2" />

UnhideWhenUsed="true" QFormat="true" Name="heading 3" />

UnhideWhenUsed="true" QFormat="true" Name="heading 4" />

UnhideWhenUsed="true" QFormat="true" Name="heading 5" />

UnhideWhenUsed="true" QFormat="true" Name="heading 6" />

UnhideWhenUsed="true" QFormat="true" Name="heading 7" />

UnhideWhenUsed="true" QFormat="true" Name="heading 8" />

UnhideWhenUsed="true" QFormat="true" Name="heading 9" />

Name="index 1" />

Name="index 2" />

Name="index 3" />

Name="index 4" />

Name="index 5" />

Name="index 6" />

Name="index 7" />

>

Name="index 8" />  
Name="index 9" />  
UnhideWhenUsed="true" Name="toc 1" />  
UnhideWhenUsed="true" Name="toc 2" />  
UnhideWhenUsed="true" Name="toc 3" />  
UnhideWhenUsed="true" Name="toc 4" />  
UnhideWhenUsed="true" Name="toc 5" />  
UnhideWhenUsed="true" Name="toc 6" />  
UnhideWhenUsed="true" Name="toc 7" />  
UnhideWhenUsed="true" Name="toc 8" />  
UnhideWhenUsed="true" Name="toc 9" />  
Name="Normal Indent" />  
Name="footnote text" />  
Name="annotation text" />  
Name="header" />  
Name="footer" />  
Name="index heading" />  
UnhideWhenUsed="true" QFormat="true" Name="caption" />  
Name="table of figures" />  
Name="envelope address" />  
Name="envelope return" />  
Name="footnote reference" />  
Name="annotation reference" />  
Name="line number" />  
Name="page number" />

>

Name="endnote reference" />

Name="endnote text" />

Name="table of authorities" />

Name="macro" />

Name="toa heading" />

Name="List" />

Name="List Bullet" />

Name="List Number" />

Name="List 2" />

Name="List 3" />

Name="List 4" />

Name="List 5" />

Name="List Bullet 2" />

Name="List Bullet 3" />

Name="List Bullet 4" />

Name="List Bullet 5" />

Name="List Number 2" />

Name="List Number 3" />

Name="List Number 4" />

Name="List Number 5" />

Name="Closing" />

Name="Signature" />

UnhideWhenUsed="true" Name="Default Paragraph Font" />

Name="Body Text" />

>

Name="Body Text Indent" />

Name="List Continue" />

Name="List Continue 2" />

Name="List Continue 3" />

Name="List Continue 4" />

Name="List Continue 5" />

Name="Message Header" />

Name="Salutation" />

Name="Date" />

Name="Body Text First Indent" />

Name="Body Text First Indent 2" />

Name="Note Heading" />

Name="Body Text 2" />

Name="Body Text 3" />

Name="Body Text Indent 2" />

Name="Body Text Indent 3" />

Name="Block Text" />

Name="Hyperlink" />

Name="FollowedHyperlink" />

Name="Document Map" />

Name="Plain Text" />

Name="E-mail Signature" />

Name="HTML Top of Form" />

Name="HTML Bottom of Form" />

>

Name="Normal (Web)" />

Name="HTML Acronym" />

Name="HTML Address" />

Name="HTML Cite" />

Name="HTML Code" />

Name="HTML Definition" />

Name="HTML Keyboard" />

Name="HTML Preformatted" />

Name="HTML Sample" />

Name="HTML Typewriter" />

Name="HTML Variable" />

Name="Normal Table" />

Name="annotation subject" />

Name="No List" />

Name="Outline List 1" />

Name="Outline List 2" />

Name="Outline List 3" />

Name="Table Simple 1" />

Name="Table Simple 2" />

Name="Table Simple 3" />

Name="Table Classic 1" />

Name="Table Classic 2" />

Name="Table Classic 3" />

Name="Table Classic 4" />

Name="Table Colorful 1" />

>

Name="Table Colorful 2" />

Name="Table Colorful 3" />

Name="Table Columns 1" />

Name="Table Columns 2" />

Name="Table Columns 3" />

Name="Table Columns 4" />

Name="Table Columns 5" />

Name="Table Grid 1" />

Name="Table Grid 2" />

Name="Table Grid 3" />

Name="Table Grid 4" />

Name="Table Grid 5" />

Name="Table Grid 6" />

Name="Table Grid 7" />

Name="Table Grid 8" />

Name="Table List 1" />

Name="Table List 2" />

Name="Table List 3" />

Name="Table List 4" />

Name="Table List 5" />

Name="Table List 6" />

Name="Table List 7" />

Name="Table List 8" />

Name="Table 3D effects 1" />

Name="Table 3D effects 2" />

>

Name="Table 3D effects 3" />

Name="Table Contemporary" />

Name="Table Elegant" />

Name="Table Professional" />

Name="Table Subtle 1" />

Name="Table Subtle 2" />

Name="Table Web 1" />

Name="Table Web 2" />

Name="Table Web 3" />

Name="Balloon Text" />

Name="Table Theme" />

Name="List Paragraph" />



Name="Intense Quote" />

Steambrite Supply

>

Name="Subtle Emphasis" />

Name="Intense Emphasis" />

Name="Subtle Reference" />

Name="Intense Reference" />

UnhideWhenUsed="true" Name="Bibliography" />

UnhideWhenUsed="true" QFormat="true" Name="TOC Heading" />

>

Name="Grid Table 1 Light Accent 1" />

Name="Grid Table 6 Colorful Accent 1" />

Name="Grid Table 7 Colorful Accent 1" />

Name="Grid Table 1 Light Accent 2" />

Name="Grid Table 6 Colorful Accent 2" />

Name="Grid Table 7 Colorful Accent 2" />

Name="Grid Table 1 Light Accent 3" />

Name="Grid Table 6 Colorful Accent 3" />

Name="Grid Table 7 Colorful Accent 3" />

Name="Grid Table 1 Light Accent 4" />

Name="Grid Table 6 Colorful Accent 4" />

Name="Grid Table 7 Colorful Accent 4" />

Name="Grid Table 1 Light Accent 5" />

>

Name="Grid Table 6 Colorful Accent 5" />

Name="Grid Table 7 Colorful Accent 5" />

Name="Grid Table 1 Light Accent 6" />

Name="Grid Table 6 Colorful Accent 6" />

Name="Grid Table 7 Colorful Accent 6" />

Name="List Table 1 Light Accent 1" />

Name="List Table 6 Colorful Accent 1" />

Name="List Table 7 Colorful Accent 1" />

Name="List Table 1 Light Accent 2" />

Name="List Table 6 Colorful Accent 2" />

Name="List Table 7 Colorful Accent 2" />

Name="List Table 1 Light Accent 3" />

Name="List Table 6 Colorful Accent 3" />

>

Name="List Table 7 Colorful Accent 3" />

Name="List Table 1 Light Accent 4" />

Name="List Table 6 Colorful Accent 4" />

Name="List Table 7 Colorful Accent 4" />

Name="List Table 1 Light Accent 5" />

Name="List Table 6 Colorful Accent 5" />

Name="List Table 7 Colorful Accent 5" />

Name="List Table 1 Light Accent 6" />

Name="List Table 6 Colorful Accent 6" />

Name="List Table 7 Colorful Accent 6" />

Name="Mention" />

Name="Smart Hyperlink" />

Name="Hashtag" />

Name="Unresolved Mention" />

Name="Smart Link" />

```
/* Style Definitions */  
table.MsoNormalTable  
{mso-style-name:"Table Normal";  
mso-tstyle-rowband-size:0;  
mso-tstyle-colband-size:0;
```

>

```
mso-style-noshow:yes;  
mso-style-priority:99;  
mso-style-parent:"";  
mso-padding-alt:0in 5.4pt 0in 5.4pt;  
mso-para-margin:0in;  
mso-pagination:widow-orphan;  
font-size:11.0pt;  
font-family:"Calibri",sans-serif;  
mso-ascii-font-family:Calibri;  
mso-ascii-theme-font:minor-latin;  
mso-hansi-font-family:Calibri;  
mso-hansi-theme-font:minor-latin;  
mso-bidi-font-family:"Times New Roman";  
mso-bidi-theme-font:minor-bidi;}
```

Optional

Allows unit to plug into dual standard 120 volt 20 amp wall outlets  
Video On Link!

Power Joiner Step Up Inverter Converts Dual 20 amp 120 Volt outlets to 240  
Volt 3 wire 15 amp L6-30R ReverseL6-30R

See How This HEPA Vacuum Performance Compares To The Top 70 Hepa Vacuums  
On The Market. Comparison Chart [HERE](#).

---

*Availability: This product was added to our catalog on Monday 20 April, 2026*