

>



Model Number: 1.006-713.0

Windsor 1.006-636.0 iCapsol Mini Carpet Dry Cleaning Machine ProCaps NO TANK CRB17

1.006-640.0 [1.006-713.0]

Manufacturer: Windsor Industries

Windsor iCapsol Mini Carpet Machine WIN9.840-302.0 NO TANK CRB machine
1.006-713.0

Manufacturer:
Windsor / Prochem

Compare to current or past Part Numbers:

9.840-302.0
1.006-606.0
9.840-301.0
1.006-640.0
1.006-636.0
1.006-641.0
EN4216
PC-PCEM-EA
PEM17
92921
WIN9.840-302.0
WIN-10060606
10066360
10066550
10066400
10060990
10061030
10060980
10061020
10066410
IM
IMIE17
IMX
IMXIE17
IM17
EQ IM17
577998
266098403020
192152847049
1.006-713.0
886622032007

>

SKU:
WIN 9.840-302.0

Product Description:

Windsor iCapsol Mini Carpet Machine SKU#WIN9.840-302.0 - (also marketed under Prochem ProCaps Deluxe Machine

Item Number: 9.840-301.0) The Windsor 1.006-636.0 and 1.006-640.0 iCapsol Mini carpet machine productively cleans and freshen carpet surfaces with less effort. The low moisture encapsulation carpet cleaning process removes soil while improving the overall carpet appearance. Carpet dries in about 20 minutes while reducing water and detergent consumption. The unique brush system features two counter-rotating brushes to effectively clean and agitate both sides of the carpet nap. Counter-rotating brushes life and groom the carpet pile, while the debris bin catches soil and debris. The Streamlined and compact design makes it easier for the operator to clean in congested areas.

Unit also double as a prescrubbing machine after you pre-spray and before you rinse with your hot water extraction machine (truckmount or portable)

Counter rotation make the unit glide over the dirtiest carpets. Very few calories burned here. This is ultra smooth cleaning...

Windsor Brochure
Sales Brochure
Owners Manual

Product Specifications:

Height: 45.5" (1160 mm) Handle Height ; 6" (153 mm) Deck Height

Width: 18" (460 mm)

Depth: 15.25" (390 mm)

Weight: 48 lbs (21.8 kg)

Motor: 0.5HP (370 watts)

Cleaning Path: 17" (430mm)

Brush Length: 2 x 16" (405 mm) offset counter-rotating, pile-lifting brushes

Brush Diameter: 3.5" (99 mm)

Brush Material and pattern: Nylon, 12 Row Chevron Pattern, special bristle trim

Brush Speed: 470 rpm

Cord Length: 40' (12 m)

Cord Wrap: Easy wrap cord/release system

Operating Height: Variable to fit operator, handle floats for operator comfort

Pump Up Sprayer Holder: Specially designed strap, rubber material secures sprayer (required)

Debris Bin: East to remove, no tools, slides out

Brush Removal: no tools, easy removal

Power Relay: Prevents unintentional start-up

>

Construction: Housing/handle and base are Impact-resistant plastic housing, aluminum handle and base
 Wheels: 3" (76.2 mm), gray non-marking
 Use weight 51 lbs with tank and sprayer / 48 lbs basic scrubber (this model).
 Shipping 64 lbs
 41"L X 20-1/2" W X 19"H
 The iCapsol interim carpet cleaning process cleans carpets faster, improves the appearance and keeps the carpet cleaner longer.
 Cleaning carpet quickly in a 24/7 environment is the challenge you face.
 With deep extraction, the carpet dries slowly due to lack of airflow through the carpet fibers that are constructed of dense loops.
 With the iCapsol Encapsulating cleaning technology, we provide a way to get your carpet cleaner faster, and with longer lasting results.
 The iCapsol Encapsulating Interim Cleaning chemical breaks down and then surrounds the soil and other detergent residue from previous cleaning.
 It dries into a hard, non-sticky crystal, encasing the soil, in about 20 minutes.
 The dried crystals can easily be removed by vacuuming.
 The low moisture chemical process dries quickly and does not leave behind sticky detergents or chemicals that will attract dirt and result in rapid re-soiling.
 The result is carpet that is clean and dry in about 20 minutes.
 • Productively clean and freshen up carpet surfaces with less effort
 • Designed to be used with Encapsulation Interim Carpet Cleaning Chemicals
 • iCapsol technology encapsulates the soil in microcrystals that are non-sticky and won't attract more soil.
 The residue is easily vacuumed when carpet is dry
 • Low moisture encapsulation carpet cleaning process removes soil while improving the overall carpet appearance; carpet dries in about 20 minutes while reducing water and detergent consumption
 • Unique brush system features two counter-rotating brushes to effectively clean and agitate both sides of the carpet nap
 • Counter-rotating brushes lift and groom the carpet pile, while the debris bin catches soil and debris
 • Streamlined, compact design makes it easier for the operator to clean in congested areas

Please note the machine ships in gray, blue, or yellow. The exact shade or color is not guaranteed as machines are shipped by part number and not by the color or sticker that is on the machine.

Compare with other CBR machines [HERE](#)
 .Optional

Karcher RM 760 Carpet Cleaning iCapsol Tablets 200 Count 6.290-500.0

>

Encapsulation No Rinse Technology 6.296-025.0

Karcher RM 760 Carpet Cleaning iCapsol Tablets 16 Count 6.290-828.0
Encapsulation No Rinse Technology 6.295-850.0

Solo 456HD-C Chemical Resistant 2 Gal Plastic Sprayer Pump Up Viton
Seals Carpet Cleaner Package For Pre-Spraying and Post Spraying
Video On Link!
Includes the larger spray jet needed for fast carpet cleaning. Includes the
lubrication spray to maintain your pump up sprayer.

Our best selling dry carpet cleaning product to use with this machine.
Harvard CRB and VLM Encapsulation Cleaner Combination 20161206 Done
Dry Plus Control
Mix and apply bone dry on carpet. Apply small amount on Control adsorbent
powder on top of Bone Dry.
Agitate both products together with ICapsol Mini while wet and again once
dried up.
Post vacuum as normally scheduled for your building.

Prochem ProCap Area Rug Wool Carpet High Low Nylon Yellow .006 Denier
Roller Brush for Icap Machine 8.629-774.0
This is a much softer brush with thinner denier filaments.

>

Superline retail 2018 = \$2019.00
Infonet \$1275 + shipping
https://www.fishmansupply.com/store/index.php?c=EQUI1300_1304 \$1910.00

-->

Availability: This product was added to our catalog on Friday 01 February, 2013