

>



Model Number: 29001

J.E. Adams 29001 Ultra Series Vacuum with Shampoo and Spot Remover Vault Ready Combination Unit

Manufacturer: J.E. Adams

Combination Unit
Car Wash and Auto Detailing

Features:

Large digital display timer is highly visible and easy to read, scrolls messages, calculates time between functions, recalculates remaining time when switched during any function, and has a built-in coin counter

Visual and audible last coin alarm

Mars Series 2000 bill acceptor takes \$1.00, \$2.00, and \$5.00 bills

Imonex electronic coin acceptor takes U.S. \$1.00 coins, U.S. quarters, 1.073 and 0.984 tokens

Comes with 7 Medeco locks (3 for the control door, 1 for an internal bill acceptor locking box,

1 for an internal coin acceptor locking box, and 2 for the shampoo & spot remover formula compartment)

3 lighted push buttons for the following functions: 2 motor vacuum,

3 motor turbo vacuum, and shampoo/spot remover settings

Lighted dome available in red, blue, yellow, dark green, light green, purple, and white

Comes with 1 gallon each of J.E. Adams's premixed formulas: shampoo and spot remover

Dispenses 2.5 gallons of foam per minute, 2 oz. of shampoo or spot remover makes 5 gallons of foam

Digital display can be easily programmed with optional remote control

Hose: 25' x 1.5", swivel cuff and nozzle included (1.5", 2.5", and 5" available in 1 1/2" or 2")

Optional coin mechs, motors, colored hoses, extra security, and clean-out container are available

[Print Brochure](#)

[Print Manual](#)

[Print Fragrance Data Sheet](#)

[Print Shampoo Data Sheet](#)

[Print Spot Remover Data Sheet](#)

>

Category:
Car Wash

Line:
Combination Units

Model #:
29001

Shipping Weight:
287.00 lb.

Description:

This unit comes standard with the following features (unless noted) and identifies replacement products:

- (3) 1.6 HP, 120 volt motors
 - Requires 30 AMP service
- Large digital display timer is highly visible and easy to read, scrolls messages, calculates time between functions, recalculates remaining time when switched during any function, and has a built-in coin counter
 - Visual and audible last coin alarm
 - Mars Series 2000 bill acceptor takes \$1.00, \$2.00, and \$5.00 bills
 - Imonex electronic coin acceptor takes U.S. \$1.00 coins, U.S. quarters, 1.073 and 0.984 tokens
 - Comes with 7 Medeco locks (3 for the control door, 1 for an internal bill acceptor locking box, 1 for an internal coin acceptor locking box, and 2 for the shampoo & spot remover formula compartment)
 - 3 lighted push buttons for the following functions: 2 motor vacuum, 3 motor turbo vacuum, and shampoo/spot remover settings
 - Lighted dome available in red, blue, yellow, dark green, light green, purple, and white
 - Digital display can be easily programmed with remote control which is available at a nominal charge
 - Hose: Black, 2" x 15', swivel cuff and nozzle included (25' and 50' also available in 1 1/2" or 2" for additional charge).
 - 2" x 15' hose available in red, blue, yellow, green, and beige at no additional charge.

>

- Optional decal packages at no additional fee - Yellow, Blue, Black (standard).
- Optional accessories available at an additional charge: Electronic Coin Acceptors, Quiet Motors, Vinyl Clean-out Bag, or Rubber Clean-out Container
- Comes with 1 gallon each of J.E. Adams's premixed formulas: shampoo and spot remover
- Shampoo & Spot Remover dispenses 2.5 gallons of foam per minute, which is equal to 1 oz of liquid formula. 1 gallon of liquid formula = 128 oz and the dispensing rate is 1 oz per minute. One gallon of liquid formula yields 128 minutes of vend time.

VAULT READY DESCRIPTION: There are two primary ways to store coins in a self-serve environment; either inside the equipment in a coin box or in a vault that is installed beneath the meter to collect coins. Vaults can hold anywhere from \$700 in quarters for the 10-inch model up to \$1600 for the 18-inch (10", 14", and 18" vaults available for sale). Since most vaults are cemented or bricked in on all sides they are very difficult for thieves to break into.

Also marketed as Part VAA29001

Availability: This product was added to our catalog on Friday 20 May, 2011